


**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY  
DIMENSIONS ARE IN mm [INCHES]

EXPANSION POWER	10X
DESIGN WAVELENGTH	1030 - 1100nm
CENTER WAVELENGTH	1064 ± 1nm
ENTRANCE BEAM MAX DIAMETER	3.00mm
INPUT APERTURE DIAMETER	8.00mm

 <b>Edmund Optics</b>			
TITLE	10X, 1064nm Draconis™ Nd:YAG Laser Line Beam Expander		
DWG NO	59130	REV	00