



# TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES



SPOT DIAGRAM

45208  
TUE DEC 16 2008 UNITS ARE  $\mu\text{m}$ .  
FIELD : : 31.741  
RMS RADIUS : : 79.472  
SCALE BAR : : 200



REFERENCE : CHIEF RAY

EDMUND OPTICS  
HTTP://WWW.EDMUNDOPTICS.COM

45208  
TUE DEC 16 2008  
MAXIMUM FOCAL SHIFT RANGE: 64.5524  $\mu\text{m}$   
DIFFRACTION LIMITED RANGE: 6.285  $\mu\text{m}$   
PUPIL ZONE: 0.0000

CHROMATIC FOCAL SHIFT

EDMUND OPTICS  
HTTP://WWW.EDMUNDOPTICS.COM



TRANSVERSE RAY FAN PLOT

45208  
TUE DEC 16 2008  
MAXIMUM SCALE:  $\pm 200.000 \mu\text{m}$ .  
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS  
HTTP://WWW.EDMUNDOPTICS.COM

45208  
TUE DEC 16 2008  
DATA FOR 0.4000 TO 0.7000  $\mu\text{m}$ .  
SURFACE: IMAGE

POLYCHROMATIC DIFFRACTION MTF

EDMUND OPTICS  
HTTP://WWW.EDMUNDOPTICS.COM



www.edmundoptics.com