



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES



SURFACE: INR
DIA: 0.000 MM
SPOT DIAGRAM

45265
TUE DEC 16 2008 UNITS ARE μm.
FIELD :
RMS RADIUS : 1.984
GD RADIUS : 2.744
SCALE BAR : 10



EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

REFERENCE : CHIEF RAY

CHROMATIC FOCAL SHIFT

45265
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 512.2124 μm
DIFFRACTION LIMITED RANGE: 150.388 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



TRANSVERSE RAY FAN PLOT

45265
TUE DEC 16 2008
MAXIMUM SCALE: ± 50.000 μm.
0.486 0.588 0.656

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

SURFACE: IMAGE

POLYCHROMATIC DIFFRACTION MTF

45265
TUE DEC 16 2008
DATA FOR 0.4000 TO 0.7000 μm.
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



www.edmundoptics.com