



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy



TECHSPEC® ACHROMATIC LENSES



SURFACE: IMAGE
DIA: 0.000 MM
SPOT DIAGRAM
45418
TUE DEC 16 2008 UNITS ARE μm.
FIELD : 1
RMS RADIUS : 14.687
GD RADIUS : 33.100
SCALE BAR : 100
REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM
45418
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 1170.1489 μm
DIFFRACTION LIMITED RANGE: 37.531 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



TRANSVERSE RAY FAN PLOT
45418
TUE DEC 16 2008
MAXIMUM SCALE: ± 500.000 μm.
0.486 0.588 0.656
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM
45418
TUE DEC 16 2008
DATA FOR 0.4000 TO 0.7000 μm.
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



www.edmundoptics.com