



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy



TECHSPEC® ACHROMATIC LENSES



SURFACE: INA
DIA: 0.000 MM
SPOT DIAGRAM
45818
TUE DEC 16 2008 UNITS ARE μm.
FIELD : :
RMS RADIUS : 1.703
GD RADIUS : 3.608
SCALE BAR : 10
REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM
45818
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 126.7947 μm
DIFFRACTION LIMITED RANGE: 46.321 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



TRANSVERSE RAY FAN PLOT
45818
TUE DEC 16 2008
MAXIMUM SCALE: ± 50.000 μm.
0.486 0.588 0.656
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM
45818
TUE DEC 16 2008
DATA FOR 0.4000 TO 0.7000 μm.
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



www.edmundoptics.com