



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES



SURFACE: INA
DIA: 0.000 MM
SPOT DIAGRAM

49316INK
TUE DEC 16 2008 UNITS ARE μm .
FIELD :
RMS RADIUS : 2.274
GD RADIUS : 6.159
SCALE BAR : 20



REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

49316INK
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 225.2072 μm
DIFFRACTION LIMITED RANGE: 37.576 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

CHROMATIC FOCAL SHIFT



SURFACE: IMAGE

49316INK
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 50.000 \mu\text{m}$.
0.486 0.588 0.656

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

49316INK
TUE DEC 16 2008
DATA FOR 0.4000 TO 1.0000 μm .
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

POLYCHROMATIC DIFFRACTION MTF



www.edmundoptics.com