



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy



TECHSPEC® ACHROMATIC LENSES



SURFACE: IMA
DIA: 0.000 MM
SPOT DIAGRAM
49344INK
TUE DEC 16 2008 UNITS ARE μm.
FIELD :
RMS RADIUS : 5.246
GD RADIUS : 11.378
SCALE BAR : 40
REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM
49344INK
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 400.8711 μm
DIFFRACTION LIMITED RANGE: 26.039 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



TRANSVERSE RAY FAN PLOT
49344INK
TUE DEC 16 2008
MAXIMUM SCALE: ± 200.000 μm.
0.486 0.588 0.656
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM
49344INK
TUE DEC 16 2008
DATA FOR 0.4000 TO 1.0000 μm.
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



www.edmundoptics.com