





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



REV. A	VALUE
SHAPE	PLANO
TRANSMISSION WAVELENGTH	671 - 790
DURABILITY	MIL-C-48497A
CUT-ON WAVELENGTH	659
SURFACE FLATNESS	>95
SURFACE QUALITY	60-40
CLEAR APERTURE	Ø45.3
BEVEL	PROTECTIVE AS NEEDED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



THIRD ANGLE PROJECTION 	TITLE	Ø50mm, 659nm, DICHROIC LASER BEAM COMBINER	
ALL DIMS IN mm	DWG NO	86402	SHEET 1 OF 1