



NOTES:

- 1. SUBSTRATE MATERIAL
SCHOTT: N-BK7 517/642
- 2. COATING (APPLY ACROSS CLEAR APERTURE)
S1: NONE
S2: VIS 0°
Ravg ≤ 0.4% @ 425 - 675nm

3. FINE GRIND SURFACE

4. RoHS COMPLIANT




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SHAPE	PLANO	PLANO
ANGLE TOL.	±15	±15
SURFACE QUALITY	40-20	40-20
SURFACE FLATNESS	λ/8	λ/8
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION



ALL DIMS IN

mm



TITLE

30mm, VIS 0° COATED, BBAR COATED RIGHT ANGLE PRISM

DWG NO

84511

SHEET 1 OF 1