



NOTES:

1. SUBSTRATE:
N-BK7
2. S2 TO BE PARALLEL WITH S1 TO <1 arcmin
3. COATING (APPLY ACROSS CLEAR APERTURE)
S1 & S2: RABS ≤0.25% @ 880nm RAVG ≤1.25% @ 400 - 870 nm RAVG ≤1.25% @ 890 - 1000nm

△ 4. FINE GRIND SURFACE

5. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2							Edmund Optics® 25mm DIA., 4mm THICK, VIS-NIR COATED λ/4 N-BK7 WINDOW	
SHAPE	PLANO	PLANO								
SURFACE QUALITY	60-40	60-40	ALL DIMS IN	mm	DWG NO	45661	SHEET 1 OF 1			
WAVELENGTH RANGE	400 - 1000nm	400 - 1000nm								
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED								