




NOTES:


- 1. SUBSTRATE:  
POLYCARBONATE
- 2. EDGES CUT AND SEAMED
- 3. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
WAVELENGTH RANGE	400 - 1600nm	400 - 1600nm
DIFFUSING ANGLE (FWHM)	0.2 x 40 ±1 x ±4°	0.2 x 40 ±1 x ±4°
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED



ALL DIMS IN mm

TITLE	0.2 x 40° DIFFUSING ANGLE 8" x 8" UNMOUNTED
DWG NO	48000
SHEET 1 OF 1	