



NOTES:

1. SUBSTRATE MATERIAL: N-BK7
2. ROHS COMPLIANT
3. COATING (APPLY ACROSS CLEAR APERTURE)
  - S1: PROTECTED ALUMINUM  
R(avg) >85% @ 400 - 700nm  
DENSITY LIMIT 0.3 J/cm<sup>2</sup> @ 532nm & 1064nm, 10ns
  - S2: UNCOATED

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**


 FINE GROUND SURFACE



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SHAPE	PLANO	PLANO
ANGLE TOL. (arcmin)	2	2
SURFACE QUALITY	40-20	60-40
SURFACE FLATNESS	$\lambda/8$	$\lambda/8$
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE  
PROJECTION



ALL DIMS IN

mm

 **Edmund Optics<sup>®</sup>**

TITLE

15mm ALUMINUM COATED DOVE PRISM

DWG NO

45815

SHEET  
1 OF 1