


FOCAL LENGTH (EFL): $9 \pm 0,09$
 BACK FOCAL LENGTH (BFL): 7,29

1 AR COATING: NONE

| LEFT SURFACE | | MATERIAL | RIGHT SURFACE | |
|--------------|----------------------------|----------------------------|---------------|----------------------------|
| R | $4,13 \pm 0,004$ CX | GLASS FUSED SILICA 458/678 | R | ∞ PL |
| Øe | 5,4 | | Øe | 5,4 |
| 3/ | 3 (0,5) $\lambda=632,8$ nm | | 3/ | 3 (0,5) $\lambda=632,8$ nm |
| 4/ | - | | 4/ | 6,55' |
| 5/ | 40 - 20 (MIL-PRF-13830B) | | 5/ | 40 - 20 (MIL-PRF-13830B) |
| 6/ | - | | 6/ | - |

| | | | | | |
|--|-------------|------------------------|--|--------------|--|
| PROTECTIVE CHAMFERS AS NEEDED | | FIRST ANGLE PROJECTION |  | | |
| ROHS: COMPLIANT | SCALE: NONE | | | | |
| SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY | | | TITLE 6mm Dia, x 9mm FL Uncoated, UV Plano-Convex Lens DWG NO 45690 | | |
| FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING | | | | | |
| INDICATIONS IN ACCORDANCE WITH ISO 10110 | | ALL DIMS IN: mm | SHEET SIZE A4 | SHEET 1 OF 1 | |