



FOCAL LENGTH (EFL): 72 ± 0,72  
 BACK FOCAL LENGTH (BFL): 70,68

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	37,21±0,037 CX	GLASS N-BK7 517/642	R	∞ PL
Øe	8,1		Øe	8,1
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION					
ROHS: COMPLIANT	SCALE: NONE					λ = 587,6nm	
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	9,0mm Dia, x 72,0mm FL, Uncoated, Plano-Convex Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				ALL DIMS IN:	mm	DWG NO	67148
INDICATIONS IN ACCORDANCE WITH ISO 10110					SHEET SIZE	A4	SHEET 1 OF 1