


NOTES:

1. SUBSTRATE: SCHOTT RG665
2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN 1 ARCMIN

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

|                        | VALUE                |
|------------------------|----------------------|
| SHAPE                  | PLANO                |
| CUT-ON WAVELENGTH (nm) | 665 ±6               |
| PASSBAND LIMIT 1 (nm)  | 750                  |
| STOPBAND LIMIT (nm)    | 580                  |
| SURFACE QUALITY        | 60-40                |
| CLEAR APERTURE         | 48.50 x 48.50        |
| BEVEL MAX FACE         | PROTECTIVE AS NEEDED |

**EO**® Edmund Optics®

|                        |        |  |                 |
|------------------------|--------|--|-----------------|
| THIRD ANGLE PROJECTION | TITLE  | SCHOTT RG665 50 x 50mm COLORED<br>LONGPASS FILTER, 2mm THK |                 |
| ALL DIMS IN            | DWG NO | mm   | 14521           |
|                        |        |  | SHEET<br>1 OF 1 |