


NOTES:

- 1. SUBSTRATE: SAPPHIRE
- 2. RoHS: COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® **Edmund Optics**®

	VALUE
DESIGN WAVELENGTH (nm)	1070
INPUT DIAMETER, 1/e <sup>2</sup> (mm)	8-12
WAVELENGTH RANGE (NM)	1020 - 1100



ALL DIMS IN mm

TITLE	1070nm, 8-12mm Dia. Input Beam, HP Sapphire Focal Flat Top Beam Shaper   Focal πShaper_1070_Q-10_HP	
DWG NO	17593	SHEET 1 OF 1