

| <b>Custom Part Restricted Countries</b> | <b>Fully Restricted Countries</b> |
|---|-----------------------------------|
| Algeria                                 | Afghanistan                       |
| Belarus                                 | Burkina Faso                      |
| Belize                                  | Burundi                           |
| Benin                                   | Cameroon                          |
| Bolivia                                 | Central African Republic          |
| Colombia                                | Chad                              |
| Congo (Republic of)                     | Congo (Democratic Republic)       |
| Cote d'Ivoire                           | Cuba                              |
| Djibouti                                | Eritrea                           |
| Ecuador                                 | Iran                              |
| Egypt                                   | Iraq                              |
| Ethiopia                                | Lebanon                           |
| Kazakhstan                              | Libya                             |
| Morocco                                 | Mali                              |
| Pakistan                                | Mauritania                        |
| Russia                                  | Myanmar (Burma)                   |
| Saudi Arabia                            | Niger                             |
| Tajikistan                              | Nigeria                           |
| Tunisia                                 | North Korea                       |
| Ukraine                                 | Palestine                         |
| Venezuela                               | Somalia                           |
| Western Sahara                          | South Sudan                       |
|   | Sudan                             |
|   | Syria                             |
|   | Yemen                             |
|   | Zimbabwe                          |