

0.22 NA UV/VIS Patchcord 400 Micron Fiber w/ FC Connector



Stock #23-709 ☐ In Stock

-

1

+

\$252.00

ADD TO CART

Qty 1-4
\$252.00
Qty 5+
\$227.00
Volume Pricing
Request Quote

Get Product Downloads

Connector:
FC/PC

Numerical Aperture NA:
0.22

Core Diameter (µm):
400

Wavelength:
UV-VIS

Length (m): 1.5
Operating Temperature (°C): -40 to +100
Type: Patchcord
Jacket Material: PVC MONOCOIL (0.190" OD)
Coating Type: Nylon
Fiber Cable Type: Multimode

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View