



12.5mm H x 25mm L x -75mm FL VIS-NIR Coated, Illumination Grade PCV Cylinder Lens



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock **#69-840** ☐ In Stock

-

1

+

\$82.00

ADD TO CART

Qty 1-5

\$82.00

Qty 6+

\$65.50

Volume Pricing

[Request Quote](#)

Get Product Downloads



Effective Focal Length EFL (mm):
-75.00

Substrate: ☐
[N-BK7](#)

Coating:
VIS-NIR (400-1000nm)

Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 400 - 1000
Back Focal Length BFL (mm): -76.65
Center Thickness CT (mm): 2.50
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 12.5 x 25.0
Edge Thickness ET (mm): 2.96
Focal Length Tolerance (%): ±3
Radius R₁ (mm): -38.76
Surface Quality: 60-40
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant