

TECHSPEC[®] 15 x 15mm Enhanced Aluminum, λ/20 Mirror



Stock #34-357 [CONTACT US](#)

-

1

+

\$126.00

ADD TO CART

Qty 1-5
\$126.00
Qty 6+
\$101.00
Volume Pricing
Request Quote

Get Product Downloads



Surface Flatness (P-V):
λ/20 (flatness pre-coating)

Substrate: [Fused Silica](#) (Corning 7980)

Back Surface:
Commercial Polish

Surface Quality:

20-10
Dimensions (mm): 15.0 x 15.0 +0.00/-0.20
Coating Specification: R _{avg} >95% @ 450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Clear Aperture (%): 90.00
Edges: Ground, protective bevel as needed
Parallelism (arcsec): 30.00
Thickness (mm): 3.00
Type: Flat Mirror
Wavelength Range (nm): 450 - 650
Length (mm): 15.00
Width (mm): 15.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant