

625nm, Strobed, Coaxial LED Spot Light

See More by [Advanced Illumination](#)



Stock **#83-306** [CONTACT US](#)



1



\$627.00

ADD TO CART

Qty 1+

\$627.00

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
Red

Model Number:
SL112-625-I3S

Operating Temperature (°C):
0 to 60

Wavelength (nm):
625.00

Weight (g): 42.5
LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Light Distribution (%): ±10
Number of LEDs: 1 High Brightness
Length of Cable (m): 1.5
Type of Illumination: LED Illuminator
Manufacturer: Advanced Illumination
Geometry: Spot Light
Illumination Mode: Strobed

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)