

TECHSPEC® 65mm X-Y Positioning Stage



65mm X-Y Positioning Stage

Stock #12-832 ☐ In Stock

⊖

1

⊕

\$477.00

ADD TO CART

Qty 1-4

\$477.00

Qty 5+

\$444.80

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:
Linear (X-Y)

Guide System:
Ball Slide

Type of Drive:
Rack and Pinion

Drive Orientation:

Center Drive
Type: Universal
Travel (mm): 25 (±12.5mm) in X and Y
Travel (inches): 0.98 (±0.49) in X and Y
Load Capacity, Normal (kg): 5
Mounting Threads: (4) M4 x0.7
Note: Movement
Straight Line Accuracy (µm): 50
Travel Per Knob Rotation (mm): 18

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View