

Allied Vision Alvium 1800 U-052c, 1/1.7" 0.5MP CS-Mount, USB 3.1 Color Camera

See More by [Allied Vision](#)



Allied Vision Alvium USB 3.1 Cameras



Stock **#23-163** ☐ In Stock

[Similar Cameras](#)

-

1

+

\$462.00

ADD TO CART

Qty 1+

\$462.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Video Output:
USB 3.1 Gen 1

Type:
Color Camera

Manufacturer:
Allied Vision

Mounting Threads: ¼-20 and M6 with Tripod Mount Adapter #14-156
Image Buffer: 256KB
Camera Family: Alvium
Model Number: 1800 U-052c
Imaging Sensor: Sony IMX426
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1/1.7"
Resolution (MegaPixels): 0.52
Pixels (H x V): 816 x 624
Pixel Size, H x V (µm): 9 x 9
Sensing Area, H x V (mm): 7.3 × 5.6
Frame Rate (fps): 691.00
Pixel Depth: 8/10/12 bit
Exposure Time: 21µs - 10s
Connector: USB 3.1 Gen 1, Micro-B
Power Supply: Power over USB or via GPIO
Power Consumption (W): 4.00
GPIOs: 4 Programmable TTL GPIOs
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 33 x 29 x 29 (includes connectors and lens mount)
Weight (g): 65
Mount: CS-Mount
Housing: Full
Interface Port Orientation: Back Panel
Operating Temperature (°C): -20 to +65 (housing temperature)
Storage Temperature (°C): -20 to +85
GPIO Connector Type: 7-pin JST
Machine Vision Standard: USB3 Vision v1.0, GenICam

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant