

Blue M37 x 0.75 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-554 ☒ In Stock



1



\$155.00

ADD TO CART

Qty 1-9

\$155.00

Qty 10+

\$147.30

Volume Pricing

[Request Quote](#)

Get Product Downloads

Blocking Wavelength Range (nm):

200-400, 550-1209

Clear Aperture CA (mm):

32.50

Coating:

Hard Coated

Filter Thread:

M37 x 0.75
Color: Blue
Center Wavelength CWL (nm): 470.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 85.00
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0
Outer Diameter (mm): 39.00
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View