

Mounted M30.5 x 0.5 Threaded - Red Filter



Stock #46-545 ☐ In Stock

1

\$53.50

ADD TO CART

Qty 1-9
\$53.50
Qty 10+
\$49.40
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm): 27.0
Filter Thread: M30.5 x 0.50
Color: Red
Cut-On Wavelength (nm): 600.00

Glass/Filter Number: R-60
Index of Refraction n_d: 1.53
Note: AR Coating: MgF ₂
Outer Diameter (mm): 32.0
Substrate: ☐ Colored Glass
Substrate Thickness (mm): 2.0
Surface Quality: 80-50
Thickness of Compatible Optics (mm): 2.0
Thickness with Mount (mm): 5.00
Type: Mounted Imaging Filter
Type of Filter: Hoya R-60 or equivalent
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View