



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES



SURFACE: IMA
 IMA: 0.000 MM
SPOT DIAGRAM

45216
 TUE DEC 16 2008 UNITS ARE μm .
 FIELD :
 RMS RADIUS : 3.720
 GEO RADIUS : 6.720
 SCALE BAR : 20



EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

REFERENCE : CHIEF RAY

CHROMATIC FOCAL SHIFT

45216
 TUE DEC 16 2008
 MAXIMUM FOCAL SHIFT RANGE: 2100.1329 μm
 DIFFRACTION LIMITED RANGE: 601.633 μm
 PUPIL ZONE: 0.0000

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



TRANSVERSE RAY FAN PLOT

45216
 TUE DEC 16 2008
 MAXIMUM SCALE: $\pm 100.000 \mu\text{m}$.
 0.486 0.588 0.656

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

SURFACE: IMAGE

POLYCHROMATIC DIFFRACTION MTF

45216
 TUE DEC 16 2008
 DATA FOR 0.4000 TO 0.7000 μm .
 SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



www.edmundoptics.com