


NOTES:



1. SUBSTRATE: UV GRADE FUSED SILICA
  2. COATING (APPLY ACROSS COATING APERTURE)
- DURABILITY: MIL-C-48497A, SECT. 3.4.1

PERFORMANCE SPECIFICATIONS @ 0° AOI  
 T(AVG): ≥91% FROM 300 - 490nm  
 T(AVG): ≤ 0.01% FROM 512 - 715nm  
 CUT-OFF SLOPE: <1%  
 CUT-OFF WAVELENGTH: 500nm ± 1%

FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING



- 3. FINE GRIND SURFACE
- 4. TRANSMITTED WAVEFRONT DISTORTION RMS @ 632.8nm ≤ 1/4 λ
- 5. ROHS COMPLIANT
- 6. ARROW POINTS TOWARDS THE FILTER COATED SURFACE




SHORTPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
 DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	>80%	>80%
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION



ALL DIMS IN

mm

TITLE

500nm 25mm Diameter, OD 4 Shortpass Filter

DWG NO

84706

SHEET  
1 OF 1