



TECHSPEC® ACHROMATIC LENSES



TECHSPEC® ACHROMATIC LENSES



Surface: IMA

Spot Diagram		Edmund Optics HTTP://WWW.EDMUNDOPTICS.COM	
33921 4/24/2017 Units are μm. Field : 1 RMS radius : 429.540 GEO radius : 1049.72 Scale bar : 4000	Airy Radius: 0.9727 μm. Legend items refer to Wavelengths Reference : Chief Ray	33921.ZMX Configuration 1 of 1	

Chromatic Focal Shift		Edmund Optics HTTP://WWW.EDMUNDOPTICS.COM	
33921 4/24/2017 Maximum Focal Shift Range: 282.8527 μm Diffraction Limited Range: 4.328 μm Pupil Zone: 0.0000		33921.ZMX Configuration 1 of 1	



— Diff. Limit-Tangential — Diff. Limit-Sagittal
— 0.0000 (deg)-Tangential — 0.0000 (deg)-Sagittal

Transverse Ray Fan Plot		Edmund Optics HTTP://WWW.EDMUNDOPTICS.COM	
33921 4/24/2017 Maximum Scale: ± 2000.000 μm. 0.486 0.588 0.656		33921.ZMX Configuration 1 of 1	

Polychromatic Diffraction MTF		Edmund Optics HTTP://WWW.EDMUNDOPTICS.COM	
33921 4/24/2017 Data for 0.4861 to 0.6563 μm. Surface: Image	Legend items refer to Field positions	33921.ZMX Configuration 1 of 1	