




NOTES:

1. SUBSTRATE MATERIAL:  
BOROFLOAT®
2. CLEAR APERTURE AND COATING APERTURE  
ARE CENTERED ON SURFACES
3. COATING (APPLY ACROSS CLEAR APERTURE)  
S1: T(avg) >85% FROM 425-675nm @ 45° AOI  
R(avg) >90% FROM 750-1125nm @ 45° AOI

S2:NONE



4. FINE GRIND SURFACE

5. POWER, IRREGULARITY, AND SURFACE QUALITY  
SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
6. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. 001	S1	S2				
SHAPE	PLANO	PLANO				
SURFACE QUALITY	80-50	80-50	THIRD ANGLE PROJECTION 	TITLE		25.0 x 25.0mm, 45° AOI, Hot Mirror
SURFACE FLATNESS	4 - 6λ	4 - 6λ		DWG NO		43956
CLEAR APERTURE	21.25 x 21.25	21.25 x 21.25	ALL DIMS IN	mm	SHEET 1 OF 1	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				