



NOTES:

1. SUBSTRATE: BOROFLOAT
2. COATING (APPLY ACROSS COATING APERTURE)
 - S1: Tavg <0.5% @ 350 - 685nm
 - Tavg >85% @ 900 - 1700 nm
 - Tavg >70% @ 710 - 900 nm and 1700 - 2500nm
 - S2: NONE
3. ROHS COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® **Edmund Optics**®

	S1	S2	THIRD ANGLE PROJECTION		TITLE	Ø50mm, 700nm, CUT-ON SWIR LONGPASS FILTER
SURFACE QUALITY	80-50	80-50	ALL DIMS IN	mm	DWG NO	86447
						SHEET 1 OF 1