


NOTES:

1. SUBSTRATE: FUSED SILICA
2. COATING (APPLY ACROSS CLEAR APERTURE)
 S1: R(abs) <0.25% @ 355nm
 S2: R(abs) <0.25% @ 355nm
3. EDGES: FINE GROUND
4. CENTERING: <3-5 ARCMIN
5. ASPHERE FIGURE ERROR: 0.75 μm RMS

△ ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE)

$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS}) * Y^2}{1 + \sqrt{1 - (1+k) * (\frac{1}{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$



SECTION K-K

COEFFICIENT TABLE △ 7

COEFFICIENT	S1
k	-1.6612216
D	0.000000E+00
E	9.1674215E-05
F	-7.1663620E-08
G	3.5564738E-10
H	-1.0410485E-13
J	0.000000E+00
L	0.000000E+00

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	EFL @ 587.6μm	25	Edmund Optics®	
SHAPE	CONVEX	PLANO	BFL @ 587.6μm	18.32	25mm DIA 0.50 NA, 355nm V-COAT, ASPHERIC LENS	
RADIUS	11.462	INFINITY	THIRD ANGLE PROJECTION			
SURFACE QUALITY	60-40	60-40	ALL DIMS IN mm		DWG NO	33011
CLEAR APERTURE	22.5	22.5			SHEET 1 OF 1	
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				