

NOTES:

1. SUBSTRATE MATERIAL:  
BOROFLOAT®


2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: UV Enhanced Aluminum  
R(avg) >89% @ 250 - 450nm  
R(avg) >85% @ 250 - 700nm  
DENSITY LIMIT: 0.5 J/cm² @ 355nm, 10ns  
S2: NONE

3. POWER, IRREGULARITY, SURFACE QUALITY, AND COATING SPECIFICATIONS APPLY ACROSS CLEAR APERTURE

△ 4. FINE GROUND SURFACE

5. ROHS COMPLIANT




SECTION A-A

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

| REV. A                 | S1                   | S2                   |
|------------------------|----------------------|----------------------|
| SHAPE                  | CONCAVE              | PLANO                |
| EFFECTIVE FOCAL LENGTH | 508mm                | N/A                  |
| FOCAL LENGTH TOLERANCE | ±2%                  | N/A                  |
| APERTURE               | f/10                 | N/A                  |
| SURFACE QUALITY        | 60-40                | 60-40                |
| SURFACE FLATNESS       | λ/4                  | λ/4                  |
| BEVEL                  | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |

THIRD ANGLE PROJECTION



ALL DIMS IN

mm

**EO**® Edmund Optics®

TITLE

2" Dia, 20" FL UV Enhanced Alum., Spherical Mirror

DWG NO

43549

SHEET  
1 OF 1