


NOTES:

1. SUBSTRATE: N-BK7
2. COATING
S1 & S2: R(ABS) < 0.25% @ 1064nm
3. EDGES: FINE GRIND
4. CENTERING: <3-5 ARCMIN
5. ASPHERE FIGURE ERROR: 0.75 μm RMS

6. ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE)

$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS}) * Y^2}{1 + \sqrt{1 - (1+k) * (\frac{1}{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$



COEFFICIENT TABLE 6.	
COEFFICIENT	S1
(1/RADIUS)	1.973944E-02
k	-2.269948E+00
D	0.000000E+00
E	0.000000E+00
F	0.000000E+00
G	0.000000E+00
H	0.000000E+00
J	0.000000E+00
L	0.000000E+00

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL @ 532.8μm	100.00			
SHAPE	PLANO	CONVEX	BFL @ 532.8μm	N/A			Edmund Optics® 25mm DIA. x 100mm FL, 1064nm V-COAT, BEST FORM ASPHERIC LENS
RADIUS	INFINITY	50.66	THIRD ANGLE PROJECTION		TITLE		
SURFACE QUALITY	60-40	60-40	ALL DIMS IN	mm	DWG NO	89442	SHEET 1 OF 1
CLEAR APERTURE	Ø22.50	Ø22.50					
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					