




NOTES:

1. SUBSTRATE:  
Fused Silica (Corning 7980)
2. TEMPERATURE RANGE:  
-40 TO +170 °C

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1
SPECTRAL RANGE	200 - 1500nm
CLEAR APERTURE	$\varnothing 45.7 \pm 0.1$
DIFFUSING ANGLE	$0.5 \pm 5^\circ$
TRANSMISSION EFFICIENCY	90%

THIRD ANGLE PROJECTION

ALL DIMS IN mm

**Edmund Optics<sup>®</sup>**

TITLE

50° DIFFUSING ANGLE 50mm DIA., UV  
HOLOGRAPHIC DIFFUSER

DWG NO

48522

SHEET  
1 OF 1