


NOTES:



1. SUBSTRATE:
D-ZLAF52LA
2. NUMERICAL APERTURE: 0.64
3. COATING
S1 & S2: R(ABS) < 1.0% @ 600 - 1050nm
4. FOCAL LENGTH TOLERANCE: ±1%
5. TRANSMITTED WAVEFRONT ERROR (λ , RMS): < 0.16



SECTION A-A

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL	2.75	 Edmund Optics®	
	CONVEX	PLANO	BFL	1.50		
SHAPE	40-20	40-20	THIRD ANGLE PROJECTION		TITLE	0.64 NA 2.75mm FL 600-1050nm AR COATED, MOLDED ASPHERIC LENS
SURFACE QUALITY	Ø3.60	Ø3.60	ALL DIMS IN	mm	DWG NO	83627
CLEAR APERTURE	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				SHEET 1 OF 1
BEVEL MAX						