

NOTES:



1. SUBSTRATE MATERIAL:  
N-BK7

2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: VIS-NIR (400-1000nm)  
R(ABS) ≤0.25% @ 880nm  
R(AVG) ≤1.25% @ 400 - 870nm  
R(AVG) ≤1.25% @ 890 - 1000nm



3. FINE GROUND SURFACE

4. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL	100	 <b>Edmund Optics®</b>	25.4mm H X 25.4mm L X 100mm FL VIS-NIR, CYLINDER LENS	
SHAPE	CONVEX	PLANO	BFL	97.86			
RADIUS	51.68	INFINITY	THIRD ANGLE PROJECTION 		TITLE		
SURFACE QUALITY	60-40	60-40					
CLEAR APERTURE	22.86 x 22.86	22.86 x 22.86	ALL DIMS IN mm		DWG NO	36223	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					