

NOTES:

1. SUBSTRATE:
LIBA 2000
2. CENTERING TOLERANCE (AT 587.6nm): BEAM DEVIATION (HALF ANGLE): <25 ARCMIN
3. COATING (APPLY ACROSS COATING APERTURE)
S1: NONE
S2: NONE

4. EDGE: AS MOLDED



5. ASPHERIC SURFACE DESCRIBED BY THE FOLLOWING EQUATION AND COEFFICIENTS SHOWN IN TABLE BELOW

$$Z(Y) = \frac{\left(\frac{1}{\text{RADIUS}}\right) * Y^2}{1 + \sqrt{1 - (1+k) * \left(\frac{1}{\text{RADIUS}}\right)^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14} + M * Y^{16}$$

6. RoHS: COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

COEFFICIENT TABLE 5.	
	S1
Semi-diameter	6.25
Coefficient (1/RADIUS)	1.917913E-01
k	-7.380216E-01
D	0.000000E+00
E	2.109812E-04
F	1.679803E-06
G	4.255379E-08
H	0.000000E+00
J	0.000000E+00
L	0.000000E+00
M	0.000000E+00



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	EFL: 10.00	Edmund Optics®	
SHAPE	CONVEX	PLANO	BFL: 4.93		
RADIUS	5.214	∞			
SURFACE QUALITY	80-50	80-50	THIRD ANGLE PROJECTION 	TITLE	LENS CONDENSER 12.5mm X 10mm UNCTD TS
CLEAR APERTURE	Ø11.25	Ø11.25	ALL DIMS IN	DWG NO	36165
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	mm		SHEET 1 OF 1