


NOTES:

1. SUBSTRATE:
D-ZLAF52LA
2. NUMERICAL APERTURE: 0.6
3. COATING
S1 & S2: R (ABS) < 1.0% @ 1050 - 1600nm
4. FOCAL LENGTH TOLERANCE: ±1%
5. TRANSMITTED WAVEFRONT ERROR (λ, RMS): < 0.40



SECTION A-A

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL	10.00	Edmund Optics®	TITLE 0.60 NA 15.00mm FL 1050-1600nm AR Coated, Molded Aspheric Lens	
	CONVEX	PLANO	BFL	7.00			
SHAPE	CONVEX	PLANO	THIRD ANGLE PROJECTION		DWG NO 37107		SHEET 1 OF 1
SURFACE QUALITY	60-40	60-40	ALL DIMS IN	mm			
CLEAR APERTURE	Ø13.00	Ø13.00					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					