


NOTES:

1. SUBSTRATE:
Alumoscilate Glass Embedded with Silver Ions
2. COATING (APPLY ACROSS COATING APERTURE)
S1 & S2: BBAR (640-700nm)
R(AVG) < 0.5% @ 670nm ±30nm
3. EFL: 0.92
4. f/# : 0.92
5. NUMERICAL APERTURE: 0.55
6. DESIGN WAVELENGTH: 670nm
7. WORKING DISTANCE: 0mm
8. ROHS: COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	THIRD ANGLE PROJECTION 		TITLE	1.0mm Dia, 670nm DWL, 0.0mm WD, VIS Coated, GRIN Lens	
SHAPE	PLANO ϕ $\{CLEAR\ APERTURE\}$ $\{SHAPE\ 1\}$	PLANO ϕ $\{CLEAR\ APERTURE\}$ $\{SHAPE\ 1\}$	ALL DIMS IN	mm	DWG NO	64535	SHEET 1 OF 1
SURFACE QUALITY	$\{SURFACE\ QUALITY\}$	$\{SURFACE\ QUALITY\}$					
CLEAR APERTURE	$\{CLEAR\ APERTURE\}$	$\{CLEAR\ APERTURE\}$					