

Surface: IMA

Spot Diagram

33202 Achromatic Lens

Units are μm . Legend items refer to Wavelengths
 Field : 1
 RMS radius : 10.655
 GEO radius : 16.092
 Scale bar : 40 Reference : Chief Ray

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

zmax_33202.zmx
 Configuration 1 of 1


Chromatic Focal Shift

33202 Achromatic Lens

Maximum Focal Shift Range: 44.6513 μm
 Diffraction Limited Range: 9.393 μm
 Pupil Zone: 0.0000

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

zmax_33202.zmx
 Configuration 1 of 1



Transverse Ray Fan Plot


33202 Achromatic Lens

Maximum Scale: $\pm 20.000 \mu\text{m}$.
 0.486 0.586 0.656

Surface: Image

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

zmax_33202.zmx
 Configuration 1 of 1



Polychromatic Diffraction MTF

33202 Achromatic Lens

Data for 0.4861 to 0.6563 μm .
 Surface: Image

Legend items refer to Field positions

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

zmax_33202.zmx
 Configuration 1 of 1