

FOCAL LENGTH (EFL):  $24 \pm 0,24$   
 BACK FOCAL LENGTH (BFL): 22,65

- 1 AR COATING: VIS-NIR  
 $R(\text{ABS}) \leq 0,25\%$  AT 880nm @ 0° AOI  
 $R(\text{AVG}) \leq 1,25\%$  FROM 400-870nm @ 0° AOI  
 $R(\text{AVG}) \leq 1,25\%$  FROM 890-1000nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	24,108±0,024 CX	GLASS N-BK7 517/642	R	24,108±0,024 CX
Øe	11		Øe	11
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT  
 SCALE: NONE  $\lambda = 587,6\text{nm}$

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE 12mm Dia, x 24mm FL, VIS-NIR Coated, Double-Convex Lens

DWG NO 33391

SHEET SIZE A4 SHEET 1 OF 1