



NOTES:

1. SUBSTRATE: FUSED SILICA
 2. COATING (APPLY ACROSS CLEAR APERTURE)
 - S1: NONE
 - S2: 532nm Laser AR Coating
 - R(ABS) < 0.25% @ 532nm @ 0° AOI
- DAMAGE THRESHOLD
 PULSED: 10J/cm² @ 20ns, 20Hz @ 532nm

 FINE GRIND SURFACE

4. ROHS COMPLIANT




**FOR INFORMATION ONLY:
 DO NOT MANUFACTURE
 PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
 DIMENSIONS ARE FOR REFERENCE ONLY

| REV. A | S1 | S2 |
|------------------|----------------------|----------------------|
| SHAPE | PLANO | PLANO |
| SURFACE QUALITY | 20-10 | 20-10 |
| CLEAR APERTURE | 19.08 x 13.50 | Ø13.50 |
| SURFACE FLATNESS | λ/20 | λ/20 |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |

THIRD ANGLE PROJECTION



ALL DIMS IN

mm

 **Edmund Optics®**

TITLE 15mm 1/20 WV 532nm AR CTD HT RA FS PRISM

DWG NO

37631

SHEET
1 OF 1