


NOTES:

1. SUBSTRATE: LIBA2000+
2. COATING:
S1 & S2: R(AVG) ≤ 1.75% @ 400 - 700nm
3. FOCAL LENGTH TOLERANCE: ±7%
4. CENTERING: <25 ARCMIN
5. RoHS: COMPLIANT
6. ASPHERIC SURFACE DESCRIBED BY THE FOLLOWING EQUATION AND COEFFICIENTS SHOWN IN TABLE BELOW

$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS}) * Y^2}{1 + \sqrt{1 - (1+k) * (\frac{1}{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



COEFFICIENT TABLE	
COEFFICIENT	S1
SEMI-DIAMETER	10.000000E+00
(1/RADIUS)	0.119058E+00
k	-0.958000E+00
D	0.000000E+00
E	4.314000E-05
F	-5.400000E-07
G	0.000000E+00
H	0.000000E+00
J	0.000000E+00
L	0.000000E+00

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	CONVEX	CONVEX
SURFACE QUALITY	80-50 (TYPICAL)	80-50 (TYPICAL)
CLEAR APERTURE	Ø16.00	Ø16.00
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

EFL: 16mm		 Edmund Optics®	
BFL: 9.53mm			
THIRD ANGLE PROJECTION 		TITLE	20mm Dia. x 16mm FL, MgF2 Molded Aspheric Condenser Lens
ALL DIMS IN	mm	DWG NO	35062
			SHEET 1 OF 1