


Surface: IMA

Spot Diagram

33283 Achromatic Lens

Units are μm . Legend items refer to Wavelengths
 Field : 1
 RMS radius : 1.834
 GEO radius : 3.420
 Scale bar : 10 Reference : Chief Ray

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)
 zmax_33283.zmx
 Configuration 1 of 1




Chromatic Focal Shift

33283 Achromatic Lens

Maximum Focal Shift Range: 33.2681 μm
 Diffraction Limited Range: 37.554 μm
 Pupil Zone: 0.0000

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)
 zmax_33283.zmx
 Configuration 1 of 1




Transverse Ray Fan Plot

33283 Achromatic Lens

Maximum Scale: $\pm 5.000 \mu\text{m}$.
 0.486 0.588 0.656
 Surface: Image

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)
 zmax_33283.zmx
 Configuration 1 of 1



Polychromatic Diffraction MTF

33283 Achromatic Lens

Data for 0.4861 to 0.6563 μm .
 Surface: Image
 Legend items refer to Field positions

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)
 zmax_33283.zmx
 Configuration 1 of 1