



FOCAL LENGTH (EFL): $25 \pm 0,25$
 BACK FOCAL LENGTH (BFL): $23,22$

| LEFT SURFACE | MATERIAL | RIGHT SURFACE |
|---|---|---|
| R 12,92 CX Øe 11 (λ) - 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ - | GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17 | R ∞ PL Øe 11 (λ) - 3/ 3 (0,5) λ=632,8 nm 4/ 1,93' 5/ 40 - 20 6/ - |

| | | | | | | |
|--|-------------|---|---|---|-------------|--------------|
| PROTECTIVE CHAMFERS AS NEEDED | | FIRST ANGLE PROJECTION |  Edmund Optics® | | | |
| ROHS: COMPLIANT | SCALE: NONE | | | | λ = 587,6nm | |
| SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY | |  | TITLE | 12mm Dia x 25mm FL, Uncoated, Plano-Convex Lens | | |
| FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING | | | ALL DIMS IN: | mm | DWG NO | |
| INDICATIONS IN ACCORDANCE WITH ISO 10110 | | | | SHEET SIZE | A4 | SHEET 1 OF 1 |