

FOCAL LENGTH (EFL): 200 ±2  
 BACK FOCAL LENGTH (BFL): 197,35

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	205,35±0,205 CX	GLASS N-BK7 517/642	R	205,35±0,205 CX
Øe	39		Øe	39
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT  
 SCALE: NONE λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE 40mm Dia, x 200mm FL Uncoated, Double-Convex Lens

DWG NO 33412

SHEET SIZE A4

SHEET 1 OF 1