

FOCAL LENGTH (EFL): $38 \pm 0,38$

BACK FOCAL LENGTH (BFL): $33,03$

1 AR COATING: 633nm V-COAT
 $R(\text{ABS}) < 0,25\% @ 633\text{nm} @ 0^\circ \text{AOI}$

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$17,421 \pm 0,017 \text{ CX}$	GLASS FUSED SILICA 458/678	R	$\infty \text{ PL}$
Øe	24		Øe	24
3/	3 (0,5) $\lambda=632,8 \text{ nm}$		3/	3 (0,5) $\lambda=632,8 \text{ nm}$
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT SCALE: NONE $\lambda = 587,6\text{nm}$

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

EO® Edmund Optics®

TITLE 25mm Dia, x 38mm FL 633nm V-Coat, UV PCX Lens

DWG NO 34116

SHEET SIZE A4 SHEET 1 OF 1