



FOCAL LENGTH (EFL): 25 ± 0,25  
 BACK FOCAL LENGTH (BFL): 22,94

- 1 AR COATING: UV-AR
  - R(ABS) ≤ 1,0% FROM 250-425nm @ 0° AOI
  - R(AVG) ≤ 0,75% FROM 250-425nm @ 0° AOI
  - R(AVG) ≤ 0,5% FROM 370-420nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	11,46±0,011 CX	GLASS FUSED SILICA 458/678	R	∞ PL
Øe	9		Øe	9
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT    SCALE: NONE    λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE 10mm Dia x 25mm FL, UV-AR Coated, Plano-Convex Lens

DWG NO 36695

SHEET SIZE A4 SHEET 1 OF 1