



FOCAL LENGTH (EFL): 54 ±0,54
 BACK FOCAL LENGTH (BFL): 51,6

- 1 AR COATING: UV-AR
 R(ABS) ≤ 1,0% FROM 250-425nm @ 0° AOI
 R(AVG) ≤ 0,75% FROM 250-425nm @ 0° AOI
 R(AVG) ≤ 0,5% FROM 370-420nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	24,755±0,025 CX	GLASS FUSED SILICA 458/678	R	∞ PL
Øe	17		Øe	17
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT
 SCALE: NONE
 λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE 18mm Dia x 54mm FL, UV-AR Coated, Plano-Convex Lens

DWG NO 36700

SHEET SIZE A4
 SHEET 1 OF 1