



FOCAL LENGTH (EFL):  $9 \pm 0,09$   
 BACK FOCAL LENGTH (BFL): 7,32

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	7,06±0,007 CX	GLASS N-SF11 785/258	R	$\infty$ PL
Øe	8,1		Øe	8,1
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	3,82'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT    SCALE: NONE     $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE 9,0mm Dia, x 9,0mm FL, Uncoated, Plano-Convex Lens

DWG NO 45081

SHEET SIZE A4 SHEET 1 OF 1